

Orbital shaker, Standard 1000

General purpose shaker with microprocessor control which is ideal for basic mixing applications, blotting techniques, staining and destaining. Variable speed control provides consistent, uniform shaking action. The speed is adjustable via knob with 1 to 10 dial settings and the ramping feature slowly increases speed to the set point for added safety.

- Suitable for continuous operation
- Can be used at 0 to +40 °C (maximum 80% relative humidity, non condensing), in an incubator, CO₂ incubator or cold room

Supplied with non-slip rubber mat.



Model	Standard 1000
Max. load (kg)	3,6
Orbit (mm)	15
Platform WxD (mm)	222x299
Power (W)	25
Shaking motion	Orbital
Speed (min ⁻¹)	40 - 300
Weight (kg)	10
WxDxH (mm)	280x430x102

Description	Pk	Cat. No.
Standard 1000 orbital shaker, EU-plug	1	444-2900
Standard 1000 orbital shaker, UK-plug	1	444-2901
Standard 1000 orbital shaker, CH-plug	1	444-2902

Orbital shaker, Standard 3500

General purpose shaker with microprocessor control which is ideal for basic mixing applications, bacterial suspensions, staining and destaining. Variable speed control provides consistent, uniform shaking action. The speed is adjustable via knob with 1 to 10 dial settings and the ramping feature slowly increases speed to the set point for added safety.

- Continuous operation or timer operation from 1 to 120 min
- Range of interchangeable attachments available
- Can be used at 0 to +40 °C (max. 80% relative humidity, non condensing), in an incubator, CO₂ incubator or cold room

Supplied with non-slip rubber mat but without attachments, accessories must be ordered separately. Please see entry 'Accessories VWR® Standard and Advanced series orbital shakers' for details on platforms and accessories.



Model	Standard 3500
Max. load (kg)	15,9
Orbit (mm)	19
Platform WxD (mm)	330x279
Power (W)	75
Shaking motion	Orbital
Speed (min ⁻¹)	25 - 500
Weight (kg)	20
WxDxH (mm)	356x413x146

Description	Pk	Cat. No.
Standard 3500 orbital shaker, EU-plug	1	444-2903
Standard 3500 orbital shaker, UK-plug	1	444-2904
Standard 3500 orbital shaker, CH-plug	1	444-2905